



5721 03UP61

5721 30UP61



Supports p. 84, plaques p. 86

### IP 20

Plaque grd. I-I, 92 × 157 mm, enjoliveur 45 × 45 mm, support 85 × 139 mm  
Montage en horizontal ou vertical

Emb

### Combinaisons encastrées grd. I-I, 10 A, 250 V

1		<b>Vide et va-et-vient</b>	vide - 3 / 1L	<b>5721 01UP61</b> 551 113 001	<b>5721 01UP67</b> 551 113 931	<b>5721 01UP68</b> 551 113 141
		1: Non équipée 2: Va-et-vient				
1		<b>Double va-et-vient</b>	3 / 1L - 3 / 1L	<b>5721 03UP61</b> 482 110 001	<b>5721 03UP67</b> 482 110 931	<b>5721 03UP68</b> 482 110 141
		1: Va-et-vient 2: Va-et-vient				
1		<b>Double va-et-vient et va-et-vient</b>	3+3 / 1L - 3 / 1L	<b>5721 04UP61</b> 482 111 001	<b>5721 04UP67</b> 482 111 931	<b>5721 04UP68</b> 482 111 141
		1: Double va-et-vient 2: Va-et-vient				
1		<b>Va-et-vient et poussoir inverseur</b>	3 / 1L - AR / 1L	<b>5721 05UP61</b> 482 142 001	<b>5721 05UP67</b> 482 142 931	<b>5721 05UP68</b> 482 142 141
		1: Va-et-vient 2: Poussoir inverseur				
1		<b>Double poussoir inverseur</b>	AR / 1L - AR / 1L	<b>5721 06UP61</b> 482 150 001	<b>5721 06UP67</b> 482 150 931	<b>5721 06UP68</b> 482 150 141
		1: Poussoir inverseur 2: Poussoir inverseur				
1		<b>Vide et poussoir de sonnerie</b>	vide - AR / 1L	<b>5721 29UP61</b> 482 146 001	<b>5721 29UP67</b> 482 146 931	<b>5721 29UP68</b> 482 146 141
		1: Non équipée 2: Poussoir de sonnerie				
1		<b>Va-et-vient et poussoir de sonnerie</b>	3 / 1L - AR / 1L	<b>5721 30UP61</b> 482 152 001	<b>5721 30UP67</b> 482 152 931	<b>5721 30UP68</b> 482 152 141
		1: Va-et-vient 2: Poussoir de sonnerie				
1		<b>Va-et-vient lumineux* et poussoir de sonnerie</b>	(LS) 3 / 1L - AR / 1L	<b>5721 32UP61</b> 482 162 001	<b>5721 32UP67</b> 482 162 931	<b>5721 32UP68</b> 482 162 141
		1: Va-et-vient lumineux* 2: Poussoir de sonnerie *Livrée sans voyant LED (à commander séparément, p. 77)				
1		<b>Plaques obturateurs</b>		<b>5721 07UP61</b> 378 510 001	<b>5721 07UP67</b> 378 510 931	<b>5721 07UP68</b> 378 510 141
		1: Obturateur 2: Obturateur				