




**USB Type-A + USB Type-C charger  
USB Type-C charger**

 5 720 77 - 5 725 77  
5 700 77 - 5 710 77

 5 720 72 - 5 725 72  
5 700 78 - 5 710 78

**1. USE**

For recharging portable devices such as phones, smartphones, tablets, MP3 or MP4 players, loudspeakers, watches, game consoles, powerbanks.

**2. RANGE**

USB chargers 5.0 V $\overline{\sim}$ / 3.0 A	White	Magnesium
<b>1 USB Type-A + 1 USB Type-C</b> (1 output Type-A - 1 output Type-C)	5 720 77	5 725 77
<b>1 USB Type-C</b> (2 outputs Type-C)	5 720 72	5 725 72

**3. OVERALL DIMENSIONS**


A	B	C	D
45	45	42	8.5

**4. CONNECTION**

Circuit breaker: 16 A max.



Type of terminals: with screws  
Terminal capacity: 2 x 2.5 mm<sup>2</sup>  
Stripping length: 6 mm  
Screwdriver: flat 3.5 mm

**5. TECHNICAL CHARACTERISTICS**
**■ 5.1 Mechanical characteristics**

Impact tests: IK 04  
Penetration by solid bodies/liquid: IP 40

**■ 5.2 Material characteristics**

Base: PC V-0 class  
Cover-plate: PC  
Self-extinguishing:  
850°C/30 s for insulating parts holding live parts in place.  
650°C/30 s for other insulating components.

**■ 5.3 Climatic characteristics**

Storage temperature: - 20°C to + 70°C  
Operating temperature: 0°C to + 45°C

**■ 5.4 Electrical characteristics**

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	100-240 V $\sim$
Nominal input frequency	50/60 Hz
Nominal output voltage	5.0 V $\overline{\sim}$
Nominal input current	0.3 A
Maximum output current Type-A + Type-C	3.0 A shared on A and C output
Maximum output current Type-C	3.0 A
Power consumption	15.0 W
Average efficiency in active mode	80.3 %
Stand-by power consumption	< 0.07 W
Consumption class without load and average level of efficiency: Level VI*	
Protection class	II - Low voltage

\***Nota:** European Regulation No. 278/2009 of 6 April 2009, Directive 2009/125 EC on eco-design requirements for AC/DC power supplies.

**Note :** To optimize the charging time of your device, ensure turn it off during the charging phase.

## 6. CLEANING

Surface cleaning with a cloth.  
Do not use: acetone, tar remover, trichlorethylene.

**Caution:** Always test before using other special cleaning products

## 7. STANDARDS AND APPROVALS

Compliance with installation and manufacturing standards.  
Refer to e-catalogue.