

**1. USE**


Used to control wake up/sleep scenes involving lights, roller shutters and connected socket outlets.

**2. RANGE**

Wake up/sleep wireless control.  
Supplied with rocker plate and a battery.  
Equipped with an LED indicator (configuration).  
Hidden reset button used to return to factory settings.  
1 module



White	Magnesium
5 742 73	5 742 90

**3. DIMENSIONS (mm)**



A	B	C	D
45	22.5	43	8

**4. OPERATION**



**5. TECHNICAL CHARACTERISTICS**

- **5.1 Mechanical characteristics**  
Protection against impacts: IK 04  
Protection against solid bodies and/or liquids: IP 21 D
- **5.2 Material characteristics**  
Rocker plate: ABS White RAL 9003  
ABS Magnesium painted
- Mechanism casing: PC  
Halogen-free  
UV-resistant  
Self-extinguishing: 650°C/30 s
- **5.3 Electrical characteristics**  
Powered by a CR2032 - 3 V lithium battery (supplied)  
Battery life: 8 years for 10 activations a day  
**ZigBee radio technology:** Frequency: 2.4 GHz to 2.4835 GHz  
Power level: < 100 mW
- **5.4 Climate characteristics**  
Storage temperature: 0°C to + 45°C  
Usage temperature: +5°C to + 45°C

## 6. CLEANING

Clean the surface with a cloth.  
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistant to the following products: Hexane (EN 60669-1), methylated spirit, soapy water, diluted ammonia, bleach diluted to 10%, window-cleaning products, pre-impregnated wipes.

**Caution:** Always test before using special cleaning products.



Take care to recycle the battery appropriately.

## 7. STANDARDS AND APPROVALS

The undersigned, LEGRAND, declares that the radio-electric equipment type (5 742 73/90) complies with directive 2014/53/EU.

The full text of the EU declaration of conformity is available on the following website: [www.legrandoc.com](http://www.legrandoc.com)